









ZIRCONIA ALUMINA SHAFT MOUNTED FLAP WHEEL

CHEMITOOL Zirconia Alumina Z Shaft Mounted Flap Wheel is suitable for coarse grinding with a high material removal rate and cold grinding.

- ✓ Less vibration and noise
- ✓ Flexibility
- ✓ Excellent adaptation to contours
- ✓ Coarse grinding
- ✓ High material removal
- ✓ Aggressive abrasive
- ✓ Highly resistant
- ✓ Long tool life

CHEMITOOL Zirconia Alumina Z Shaft Mounted Flap Wheel are great for work in places with bad accessibility, giving the possibility to remove the most difficult materials. Suitable for leveling and deburring edges, weld beads and surface work, structuring surfaces and fine grinding. Its flexibility allows perfect adaptation to the contours of the work piece and, consequently, a better precision. For the best results, we recommend using at speed of 15-20 m/s.

Abrasive

Zirconia Alumina Z

Suitable for

Steel, cast steel, stainless steel, brass, copper, zinc, bronze, titanium, cast iron and nickelbased and cobalt-based alloys.

Suitable Machines

Flexible Shaft Drives, Straight Grinders





SAP	Ø (mm) Shaft	*	R.P.M.	\Diamond	EAN
CHA1002030010040S6	30 x 10 x 6 6×30	40	25 000	20	5604630029209
CHA1002030010060S6	30 x 10 x 6 6×30	60	25 000	20	5604630029193
CHA1002030010080S6	30 x 10 x 6 6×30	80	25 000	20	5604630029186
CHA1002030010120S6	30 x 10 x 6 6×30	100	25 000	20	5604630029162
CHA1002040020040S6	40 x 20 x 6 6×30	120	20 000	10	5604630028561
CHA1002040020060S6	40 x 20 x 6 6×30	40	20 000	10	5604630028554
CHA1002040020080S6	40 x 20 x 6 6×30	60	20 000	10	5604630028547
CHA1002040020120S6	40 x 20 x 6 6×30	80	20 000	10	5604630028523
CHA1002050020040S6	50 x 20 x 6 6×30	40	15 000	10	5604630018395
CHA1002050020060S6	50 x 20 x 6 6×30	60	15 000	10	5604630018388
CHA1002050020080S6	50 x 20 x 6 6×30	80	15 000	10	5604630018371
CHA1002050020120S6	50 x 20 x 6 6×30	120	15 000	10	5604630018357
CHA1002060030040S6	60 x 30 x 6 6×30	40	12 500	10	5604630017848
CHA1002060030060S6	60 x 30 x 6 6×30	60	12 500	10	5604630017831
CHA1002060030080S6	60 x 30 x 6 6×30	80	12 500	10	5604630017824
CHA1002060030120S6	60 x 30 x 6 6×30	120	12 500	10	5604630017800
CHA1002080050040S6	80 x 50 x 6 6×30	40	9 500	5	5604630019132
CHA1002080050060S6	80 x 50 x 6 6×30	60	9 500	5	5604630019125
CHA1002080050080S6	80 x 50 x 6 6×30	80	9 500	5	5604630019118
CHA1002080050120S6	80 x 50 x 6 6×30	120	9 500	5	5604630019095

Note: The technical information provided, either verbally or in writing, is based on our current knowledge and should be considered as collaboration without commitment. The use of the product is beyond our control, thus, we rule out any responsibility for its improper use. The customer is responsible to confirm and validate (by testing) if the product is suitable for the process and the type of use in question. Our purpose is exclusively to guarantee the quality of the products, according to our standards.